

***SPEED
ALLOYS***

ALUMINIUM BARS & TUBES

- ◆ Round bar
- ◆ Round tube
- ◆ Square bar
- ◆ Hexagonal bar
- ◆ Flat bar
- ◆ Box tube

www.speedalloys.co.uk



| Description | Size | Spec |
|---------------------|-------------|-------------|
| Aluminium Round Bar | 3MM DIA | 6082T6 |
| Aluminium Round Bar | 4MM DIA | 6082T6 |
| Aluminium Round Bar | 5MM DIA | 6082T6 |
| Aluminium Round Bar | 1/4" DIA | 7075T651 |
| Aluminium Round Bar | 1/4" DIA | 6082T6 |
| Aluminium Round Bar | 6MM DIA | 6082T6 |
| Aluminium Round Bar | 5/16" DIA | 2011T3 |
| Aluminium Round Bar | 11/32" DIA | 2011T3 |
| Aluminium Round Bar | 11/32" DIA | 2014AT4 |
| Aluminium Round Bar | 5/16" DIA | 6082T6 |
| Aluminium Round Bar | 8MM DIA | 6082T6 |
| Aluminium Round Bar | 3/8" DIA | 2014AT6 |
| Aluminium Round Bar | 3/8" DIA | 6082T6 |
| Aluminium Round Bar | 10MM DIA | 2011T3 |
| Aluminium Round Bar | 10MM DIA | 6082T6 |
| Aluminium Round Bar | 7/16" DIA | 2011T3 |
| Aluminium Round Bar | 7/16" DIA | 7075T6 |
| Aluminium Round Bar | 1/2" DIA | 2011T3 |
| Aluminium Round Bar | 1/2" DIA | 7075T651 |
| Aluminium Round Bar | 1/2" DIA | 6082T6 |
| Aluminium Round Bar | 12MM DIA | 6082T6 |
| Aluminium Round Bar | 17/32" DIA | 6082T6 |
| Aluminium Round Bar | 9/16" DIA | 2011T3 |
| Aluminium Round Bar | 9/16" DIA | 6082T6 |
| Aluminium Round Bar | 15MM DIA | 6082T6 |
| Aluminium Round Bar | 5/8" DIA | 2011T3 |
| Aluminium Round Bar | 5/8" DIA | 2014AT6 |
| Aluminium Round Bar | 5/8" DIA | 6063T6 |
| Aluminium Round Bar | 5/8" DIA | 6082T6 |
| Aluminium Round Bar | 16MM DIA | 6082T6 |
| Aluminium Round Bar | 11/16" DIA | 2011T3 |
| Aluminium Round Bar | 18MM DIA | 6082T6 |
| Aluminium Round Bar | 3/4" DIA | 6082T6 |
| Aluminium Round Bar | 3/4" DIA | 2011T3 |
| Aluminium Round Bar | 20MM DIA | 5083 F |
| Aluminium Round Bar | 3/4" DIA | 7075 |
| Aluminium Round Bar | 13/16" DIA | 6082T6 |
| Aluminium Round Bar | 20MM DIA | 6082T6 |
| Aluminium Round Bar | 7/8" DIA | 2011T3 |
| Aluminium Round Bar | 7/8" DIA | 6082T6 |
| Aluminium Round Bar | 15/16" DIA | 6262T9 |
| Aluminium Round Bar | 1" DIA | GCQ |
| Aluminium Round Bar | 1" DIA | 2011T3 |
| Aluminium Round Bar | 1" DIA | 2014AT6 |
| Aluminium Round Bar | 25MM DIA | 5083 F |
| Aluminium Round Bar | 1" DIA | 6082T6 |
| Aluminium Round Bar | 25MM DIA | 6082T6 |
| Aluminium Round Bar | 1 1/8" DIA | 6063T6 |
| Aluminium Round Bar | 1 1/8" DIA | 2011T3 |
| Aluminium Round Bar | 1 1/8" DIA | 2014AT6 |
| Aluminium Round Bar | 1 1/8" DIA | 6082T6 |
| Aluminium Round Bar | 1 1/4" DIA | 2011T3 |
| Aluminium Round Bar | 1 3/16" DIA | 2011T3 |

| | | |
|---------------------|------------|-----------|
| Aluminium Round Bar | 1 1/4" DIA | 2014AT6 |
| Aluminium Round Bar | 30MM DIA | 5083 F |
| Aluminium Round Bar | 1 1/4" DIA | 6061T6 |
| Aluminium Round Bar | 30MM DIA | 6082T6 |
| Aluminium Round Bar | 1 1/4" DIA | 6082T6 |
| Aluminium Round Bar | 1 3/8" DIA | 6082T4 |
| Aluminium Round Bar | 1 3/8" DIA | 6082T6 |
| Aluminium Round Bar | 36MM DIA | 7075T6 |
| Aluminium Round Bar | 1 1/2" DIA | 2011T3 |
| Aluminium Round Bar | 1 1/2" DIA | 2014AT6 |
| Aluminium Round Bar | 40MM DIA | 2014AT6 |
| Aluminium Round Bar | 1 1/2" DIA | 6082T6 |
| Aluminium Round Bar | 40MM DIA | 6082T6 |
| Aluminium Round Bar | 1 5/8" DIA | 7075T6511 |
| Aluminium Round Bar | 1 5/8" DIA | 2011T3 |
| Aluminium Round Bar | 1 5/8" DIA | 2014AT6 |
| Aluminium Round Bar | 1 5/8" DIA | 6082T6 |
| Aluminium Round Bar | 1 3/4" DIA | 6063T6 |
| Aluminium Round Bar | 1 3/4" DIA | 2011T3 |
| Aluminium Round Bar | 45MM DIA | 6082T6 |
| Aluminium Round Bar | 1 7/8" DIA | 2014AT4 |
| Aluminium Round Bar | 1 7/8" DIA | 2011T3 |
| Aluminium Round Bar | 1 7/8" DIA | 2014AT6 |
| Aluminium Round Bar | 1 7/8" DIA | 6082T6 |
| Aluminium Round Bar | 2" DIA | 2011T3 |
| Aluminium Round Bar | 2" DIA | 2014AT6 |
| Aluminium Round Bar | 2" DIA | 6061T6 |
| Aluminium Round Bar | 2" DIA | 7075T7351 |
| Aluminium Round Bar | 2" DIA | 7075T651 |
| Aluminium Round Bar | 2" DIA | 6082T6 |
| Aluminium Round Bar | 2 1/8" DIA | 2011T3 |
| Aluminium Round Bar | 2 1/8" DIA | 6082T6 |
| Aluminium Round Bar | 2 1/4" DIA | 2011T3 |
| Aluminium Round Bar | 2 1/4" DIA | 2014AT6 |
| Aluminium Round Bar | 2 1/4" DIA | 5251 |
| Aluminium Round Bar | 2 1/4" DIA | 6061T6 |
| Aluminium Round Bar | 2 1/4" DIA | 7075T7351 |
| Aluminium Round Bar | 2 1/4" DIA | 7075T651 |
| Aluminium Round Bar | 2 1/4" DIA | 6082T6 |
| Aluminium Round Bar | 2 3/8" DIA | 6082T6 |
| Aluminium Round Bar | 2 1/2" DIA | GCQ |
| Aluminium Round Bar | 2 1/2" DIA | 2011T3 |
| Aluminium Round Bar | 2 1/2" DIA | 6082T6 |
| Aluminium Round Bar | 65MM DIA | 2014AT6 |
| Aluminium Round Bar | 2 5/8" DIA | 6082T6 |
| Aluminium Round Bar | 70MM DIA | 6082T6 |
| Aluminium Round Bar | 2 3/4" DIA | 2014AT6 |
| Aluminium Round Bar | 70MM DIA | 2618A |
| Aluminium Round Bar | 2 3/4" DIA | 6082T6 |
| Aluminium Round Bar | 2 7/8" DIA | GCQ |
| Aluminium Round Bar | 2 7/8" DIA | 2011T3 |
| Aluminium Round Bar | 2 7/8" DIA | 2014 |
| Aluminium Round Bar | 3" DIA | GCQ |
| Aluminium Round Bar | 3" DIA | 2024T3 |
| Aluminium Round Bar | 75MM DIA | 6082T6 |

| | | |
|---------------------|------------|-----------|
| Aluminium Round Bar | 3" DIA | 2011T6 |
| Aluminium Round Bar | 3" DIA | 2011T3 |
| Aluminium Round Bar | 3" DIA | 5083 |
| Aluminium Round Bar | 3" DIA | 6082T6 |
| Aluminium Round Bar | 3 1/4" DIA | 2011T6 |
| Aluminium Round Bar | 3 1/4" DIA | 2014AT6 |
| Aluminium Round Bar | 3 1/4" DIA | 5083 F |
| Aluminium Round Bar | 3 1/4" DIA | 6082T6 |
| Aluminium Round Bar | 3 1/2" DIA | 2011T6 |
| Aluminium Round Bar | 3 1/2" DIA | 2014AT6 |
| Aluminium Round Bar | 3 1/2" DIA | 7075T7351 |
| Aluminium Round Bar | 3 1/2" DIA | 7075T6 |
| Aluminium Round Bar | 3 1/2" DIA | 6082T6 |
| Aluminium Round Bar | 3 3/4" DIA | 2011T3 |
| Aluminium Round Bar | 3 3/4" DIA | 6082T6 |
| Aluminium Round Bar | 4" DIA | 2011T3 |
| Aluminium Round Bar | 4" DIA | 2030T3 |
| Aluminium Round Bar | 100MM DIA | 2031T651 |
| Aluminium Round Bar | 100MM DIA | 2618A |
| Aluminium Round Bar | 4" DIA | 7075T6 |
| Aluminium Round Bar | 100MM DIA | 7075T651 |
| Aluminium Round Bar | 4" DIA | 6082T6 |
| Aluminium Round Bar | 4 1/4" DIA | 2014AT6 |
| Aluminium Round Bar | 4 1/4" DIA | 6082T6 |
| Aluminium Round Bar | 4 1/2" DIA | 2011T3 |
| Aluminium Round Bar | 4 1/2" DIA | 2014AT6 |
| Aluminium Round Bar | 4 1/2" DIA | 6082T6 |
| Aluminium Round Bar | 4 5/8" DIA | 6082T6 |
| Aluminium Round Bar | 120MM DIA | 2024 |
| Aluminium Round Bar | 4 3/4" DIA | 6082T6 |
| Aluminium Round Bar | 125MM DIA | GCQ |
| Aluminium Round Bar | 5" DIA | 2014AT6 |
| Aluminium Round Bar | 5" DIA | 2024 |
| Aluminium Round Bar | 5" DIA | 7075 |
| Aluminium Round Bar | 5" DIA | 6082T6 |
| Aluminium Round Bar | 5 1/4" DIA | 6082T6 |
| Aluminium Round Bar | 5 1/2" DIA | 2014AT4 |
| Aluminium Round Bar | 5 1/2" DIA | 2014AT6 |
| Aluminium Round Bar | 5 1/2" DIA | 6082T6 |
| Aluminium Round Bar | 5 3/4" DIA | 6082T6 |
| Aluminium Round Bar | 6" DIA | 2014AT6 |
| Aluminium Round Bar | 150MM DIA | 5083 F |
| Aluminium Round Bar | 6" DIA | 6082T6 |
| Aluminium Round Bar | 6.1/4" DIA | 6082T6 |
| Aluminium Round Bar | 6 1/2" DIA | 2014AT6 |
| Aluminium Round Bar | 6 1/2" DIA | 6082T6 |
| Aluminium Round Bar | 170MM DIA | GCQ |
| Aluminium Round Bar | 175MM DIA | 6082T6 |
| Aluminium Round Bar | 180MM DIA | 2011T3 |
| Aluminium Round Bar | 180MM DIA | 5083 F |
| Aluminium Round Bar | 7" DIA | 6082T651 |
| Aluminium Round Bar | 7 1/4" DIA | 6082T6 |
| Aluminium Round Bar | 7 1/2" DIA | 6082T6 |
| Aluminium Round Bar | 8" DIA | 2014AT6 |
| Aluminium Round Bar | 8" DIA | 6082T6 |

| | | |
|---------------------|------------|---------|
| Aluminium Round Bar | 210MM DIA | GCQ |
| Aluminium Round Bar | 8 1/2" DIA | 6082T6 |
| Aluminium Round Bar | 9" DIA | 2014AT6 |
| Aluminium Round Bar | 9" DIA | 6082T6 |
| Aluminium Round Bar | 240MM DIA | GCQ |
| Aluminium Round Bar | 9 1/2" DIA | 6082T6 |
| Aluminium Round Bar | 10" DIA | 2014AT6 |
| Aluminium Round Bar | 10" DIA | 6082T6 |
| Aluminium Round Bar | 260MM DIA | 6082T6 |
| Aluminium Round Bar | 11" DIA | 6082T6 |
| Aluminium Round Bar | 12" DIA | 6082T6 |

| Description | Size | Spec |
|--------------------|-------------------|-------------|
| Aluminium Tube | 6MM OD X 1MM | 6063T6 |
| Aluminium Tube | 8MM OD X 1MM | 6063T6 |
| Aluminium Tube | 8MM OD X 1.5MM | 6063T6 |
| Aluminium Tube | 3/8" OD X 16G | 6063T6 |
| Aluminium Tube | 10MM OD X 1MM | 6063T6 |
| Aluminium Tube | 10MM OD X 2MM | 6063T6 |
| Aluminium Tube | 1/2" OD X 16G | 6063T6 |
| Aluminium Tube | 1/2" OD X 14G | 6082T6 |
| Aluminium Tube | 1/2" OD X 10G | 6082T6 |
| Aluminium Tube | 5/8" OD X 16G | 6063T6 |
| Aluminium Tube | 5/8" OD X 16G | 6082T6 |
| Aluminium Tube | 5/8" OD X 14G | 6082T6 |
| Aluminium Tube | 5/8" OD X 10G | 6082T6 |
| Aluminium Tube | 3/4" OD X 16G | 6063T6 |
| Aluminium Tube | 3/4" OD X 16G | 6082T6 |
| Aluminium Tube | 3/4" OD X 14G | 6082T6 |
| Aluminium Tube | 20MM OD X 2.5MM | 6063T6 |
| Aluminium Tube | 20MM OD X 2MM | 6063T6 |
| Aluminium Tube | 3/4" OD X 10G | 6082T6 |
| Aluminium Tube | 20MM OD X 3MM | 6082T6 |
| Aluminium Tube | 3/4" OD X 3/16" | 6082T6 |
| Aluminium Tube | 3/4" OD X 1/4" | 6082T6 |
| Aluminium Tube | 7/8" OD X 16G | 6063T6 |
| Aluminium Tube | 7/8" OD X 16G | 6082T6 |
| Aluminium Tube | 7/8" OD X 14G | 6082T6 |
| Aluminium Tube | 7/8" OD X 10G | 6082T6 |
| Aluminium Tube | 7/8" OD X 3/16" | 6082T6 |
| Aluminium Tube | 25.4MM OD X 1.5MM | 6063T6 |
| Aluminium Tube | 1" OD X 16G | 6063T6 |
| Aluminium Tube | 1" OD X 16G | 6082T6 |
| Aluminium Tube | 1" OD X 14G | 6082T6 |
| Aluminium Tube | 1" OD X 12G | 6082T6 |
| Aluminium Tube | 1" OD X 10G | 6082T6 |
| Aluminium Tube | 1" OD X 3/16" | 6082T6 |
| Aluminium Tube | 1" OD X 1/4" | 6082T6 |
| Aluminium Tube | 26MM OD X 2MM | 6082T6 |
| Aluminium Tube | 1.1/8" OD X 18G | 6063T6 |
| Aluminium Tube | 1 1/8" OD X 16G | 6082T6 |
| Aluminium Tube | 1 1/8" OD X 10G | 6082T6 |
| Aluminium Tube | 1 1/4" OD X 16G | 6082T6 |
| Aluminium Tube | 1 1/4" OD X 14G | 6082T6 |
| Aluminium Tube | 30MM OD X 2MM | 6082T6 |
| Aluminium Tube | 1 1/4" OD X 12G | 6063T6 |
| Aluminium Tube | 1 1/4" OD X 12G | 6082T6 |
| Aluminium Tube | 1 1/4" OD X 10G | 6082T6 |
| Aluminium Tube | 30MM OD X 3MM | 6082T6 |
| Aluminium Tube | 1 1/4" OD X 3/16" | 6082T6 |
| Aluminium Tube | 30MM OD X 5MM | 6082T6 |
| Aluminium Tube | 1 1/4" OD X 1/4" | 6082T6 |
| Aluminium Tube | 1 3/8" OD X 16G | 6082T6 |
| Aluminium Tube | 1 3/8" OD X 10G | 6082T6 |
| Aluminium Tube | 1 3/8" OD X 1/4" | 6082T6 |
| Aluminium Tube | 40MM OD X 10MM | 6082T6 |

| | | |
|----------------|-------------------|--------|
| Aluminium Tube | 1 1/2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 1 1/2" OD X 16G | 6063T6 |
| Aluminium Tube | 1 1/2" OD X 16G | 6082T6 |
| Aluminium Tube | 1 1/2" OD X 14G | 6082T6 |
| Aluminium Tube | 1 1/2" OD X 10G | 6082T6 |
| Aluminium Tube | 40MM OD X 3MM | 6082T6 |
| Aluminium Tube | 1 1/2" OD X 3/16" | 6082T6 |
| Aluminium Tube | 40MM OD X 5MM | 6082T6 |
| Aluminium Tube | 1 1/2" OD X 1/4" | 6082T6 |
| Aluminium Tube | 1 5/8" OD X 16G | 6063T6 |
| Aluminium Tube | 1 5/8" OD X 16G | 6082T6 |
| Aluminium Tube | 1 5/8" OD X 10G | 6082T6 |
| Aluminium Tube | 1 5/8" OD X 3/16" | 6082T6 |
| Aluminium Tube | 1 5/8" OD X 1/4" | 6082T6 |
| Aluminium Tube | 1 3/4" OD X 16G | 6063T6 |
| Aluminium Tube | 1 3/4" OD X 16G | 6082T6 |
| Aluminium Tube | 1 3/4" OD X 10G | 6082T6 |
| Aluminium Tube | 1 3/4" OD X 3/16" | 6082T6 |
| Aluminium Tube | 1 3/4" OD X 1/4" | 6082T6 |
| Aluminium Tube | 1 3/4" OD X 3/8" | 6082T6 |
| Aluminium Tube | 1 29/32" OD X 7G | 6082T6 |
| Aluminium Tube | 48MM OD X 1.5MM | 6082T6 |
| Aluminium Tube | 1 7/8" OD X 10G | 6082T6 |
| Aluminium Tube | 1 7/8" OD X 1/4" | 6082T6 |
| Aluminium Tube | 2" OD X 18G | 6061T6 |
| Aluminium Tube | 2" OD X 16G | 6063T6 |
| Aluminium Tube | 2" OD X 16G | 6082T6 |
| Aluminium Tube | 2" OD X 14G | 6082T6 |
| Aluminium Tube | 2" OD X 10G | 6082T6 |
| Aluminium Tube | 2" OD X 3/16" | 6082T6 |
| Aluminium Tube | 2" OD X 1/4" | 6082T6 |
| Aluminium Tube | 2" OD X 3/8" | 6082T6 |
| Aluminium Tube | 2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 2 1/4" OD X 16G | 6063T6 |
| Aluminium Tube | 2 1/4" OD X 10G | 6082T6 |
| Aluminium Tube | 2 1/4" OD X 1/4" | 6082T6 |
| Aluminium Tube | 2 1/4" OD X 3/8" | 6082T6 |
| Aluminium Tube | 2 1/4" OD X 1/2" | 6082T6 |
| Aluminium Tube | 60MM OD X 3MM | 6082T6 |
| Aluminium Tube | 60MM OD X 5MM | 6082T6 |
| Aluminium Tube | 60MM OD X 10MM | 6082T6 |
| Aluminium Tube | 2 1/2" OD X 16G | 6063T6 |
| Aluminium Tube | 2 1/2" OD X 16G | 6082T6 |
| Aluminium Tube | 2 1/2" OD X 3/4" | 6082T6 |
| Aluminium Tube | 2 1/2" OD X 10G | 6082T6 |
| Aluminium Tube | 2 1/2" OD X 3/16" | 6082T6 |
| Aluminium Tube | 2 1/2" OD X 1/4" | 6082T6 |
| Aluminium Tube | 2 1/2" OD X 3/8" | 6082T6 |
| Aluminium Tube | 2 1/2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 2 3/4" OD X 16G | 6082T6 |
| Aluminium Tube | 2 3/4" OD X 10G | 6082T6 |
| Aluminium Tube | 2 3/4" OD X 1/4" | 6082T6 |
| Aluminium Tube | 2 3/4" OD X 3/8" | 6082T6 |
| Aluminium Tube | 2 3/4" OD X 1/2" | 6082T6 |
| Aluminium Tube | 3" OD X 16G | 6063T6 |

| | | |
|----------------|------------------|--------|
| Aluminium Tube | 3" OD X 10G | 6082T6 |
| Aluminium Tube | 3" OD X 3/16" | 6082T6 |
| Aluminium Tube | 3" OD X 1/4" | 6082T6 |
| Aluminium Tube | 3" OD X 3/8" | 6082T6 |
| Aluminium Tube | 3" OD X 7/16" | 5251 |
| Aluminium Tube | 3"OD X 1/2" | 6082T6 |
| Aluminium Tube | 3" OD X 3/4" | 6082T6 |
| Aluminium Tube | 3" OD X 1" | 6082T6 |
| Aluminium Tube | 80MM OD X 5MM | 6082T6 |
| Aluminium Tube | 80MM OD X 10MM | 6082T6 |
| Aluminium Tube | 3 1/4" OD X 10G | 6082T6 |
| Aluminium Tube | 3 1/4" OD X 1/4" | 6082T6 |
| Aluminium Tube | 3 1/4" OD X 3/8" | 6082 |
| Aluminium Tube | 3 1/4" OD X 1/2" | 6082T6 |
| Aluminium Tube | 3 1/2" OD X 16G | 6082T6 |
| Aluminium Tube | 3 1/2" OD X 14G | 6082T6 |
| Aluminium Tube | 3 1/2" OD X 10G | 6063T6 |
| Aluminium Tube | 3 1/2" OD X 10G | 6082T6 |
| Aluminium Tube | 3 1/2" OD X 1/4" | 6082T6 |
| Aluminium Tube | 3 1/2" OD X 3/8" | 6082T6 |
| Aluminium Tube | 3 1/2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 3 1/2" OD X 3/4" | 6082T6 |
| Aluminium Tube | 3 1/2" OD X 1" | 6082T6 |
| Aluminium Tube | 3 3/4" OD X 1/2" | 6082T6 |
| Aluminium Tube | 4" OD X 16G | 6063T6 |
| Aluminium Tube | 4" OD X 10G | 6082T6 |
| Aluminium Tube | 4" OD X 3/16" | 6082T6 |
| Aluminium Tube | 4" OD X 1/4" | 6082T6 |
| Aluminium Tube | 4" OD X 3/8" | 6082T6 |
| Aluminium Tube | 100MM OD X 10MM | 6082T6 |
| Aluminium Tube | 4" OD X 1/2" | 6082T6 |
| Aluminium Tube | 4" OD X 3/4" | 6082T6 |
| Aluminium Tube | 4" OD X 1" | 6082T6 |
| Aluminium Tube | 4 1/4" OD X 10G | 6082T6 |
| Aluminium Tube | 4 1/2" OD X 10G | 6082T6 |
| Aluminium Tube | 4 1/2" OD X 1/4" | 6082T6 |
| Aluminium Tube | 4 1/2" OD X 3/8" | 6082T6 |
| Aluminium Tube | 4 1/2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 4 1/2" OD X 3/4" | 6082T6 |
| Aluminium Tube | 4 1/2" OD X 1" | 6082T6 |
| Aluminium Tube | 120MM OD X 3MM | 6082T6 |
| Aluminium Tube | 4 3/4" OD X 1/4" | 6082T6 |
| Aluminium Tube | 125MM OD X 2.5MM | 6082T6 |
| Aluminium Tube | 5" OD X 10G | 6082T6 |
| Aluminium Tube | 5" OD X 3/16" | 6082T6 |
| Aluminium Tube | 5" OD X 1/4" | 6082T6 |
| Aluminium Tube | 5" OD X 3/8" | 6082T6 |
| Aluminium Tube | 5" OD X 1/2" | 6082T6 |
| Aluminium Tube | 5" OD X 3/4" | 6082T6 |
| Aluminium Tube | 5" OD X 1" | 6082T6 |
| Aluminium Tube | 130MM OD X 3MM | 6082T6 |
| Aluminium Tube | 5 1/2" OD X 1/4" | 6082T6 |
| Aluminium Tube | 5 1/2" OD X 3/8" | 6082T6 |
| Aluminium Tube | 5 1/2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 140MM OD X 15MM | 6082T6 |

| | | |
|----------------|--------------------|---------|
| Aluminium Tube | 5 1/2" OD X 3/4" | 6082T6 |
| Aluminium Tube | 5 1/2" OD X 1" | 6082T6 |
| Aluminium Tube | 5 1/2" OD X 1 1/4" | 6082T6 |
| Aluminium Tube | 145MM OD X 20MM | 2014AT6 |
| Aluminium Tube | 5 3/4" OD X 1 1/4" | 6082T6 |
| Aluminium Tube | 6" OD X 1/4" | 6082T6 |
| Aluminium Tube | 6" OD X 10G | 6082T6 |
| Aluminium Tube | 6" OD X 3/8" | 6082T6 |
| Aluminium Tube | 6" OD X 1/2" | 6082T6 |
| Aluminium Tube | 6" OD X 3/4" | 6082T6 |
| Aluminium Tube | 6" OD X 1" | 6082T6 |
| Aluminium Tube | 165MM OD X 5MM | 6082T6 |
| Aluminium Tube | 6 1/2" OD 1/4" | 6082T6 |
| Aluminium Tube | 6 1/2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 6 1/2" OD X 3/4" | 6082T6 |
| Aluminium Tube | 6 1/2" OD X 1" | 6082T6 |
| Aluminium Tube | 170MM OD X 20MM | 6082T6 |
| Aluminium Tube | 7" OD X 1/4" | 6082T6 |
| Aluminium Tube | 7" OD X 3/8" | 6082T6 |
| Aluminium Tube | 180MM OD X 10MM | 6082T6 |
| Aluminium Tube | 7" OD X 1/2" | 6082T6 |
| Aluminium Tube | 180MM OD X 20MM | 6061T6 |
| Aluminium Tube | 7" OD X 3/4" | 6082T6 |
| Aluminium Tube | 7" OD X 1" | 6082T6 |
| Aluminium Tube | 183MM OD X 14MM | 6063T6 |
| Aluminium Tube | 7 1/2" OD X 1/4" | 6082T6 |
| Aluminium Tube | 7 1/2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 7 1/2" OD X 3/4" | 6082T6 |
| Aluminium Tube | 7 1/2" OD 1" | 6082T6 |
| Aluminium Tube | 8" OD X 1/4" | 6082T6 |
| Aluminium Tube | 8" OD X 3/8" | 6082T6 |
| Aluminium Tube | 200MM OD X 10MM | 6082T6 |
| Aluminium Tube | 8" OD X 1/2" | 6082T6 |
| Aluminium Tube | 8" OD X 3/4" | 6082T6 |
| Aluminium Tube | 8" OD X 1" | 6082T6 |
| Aluminium Tube | 8" OD X 1 1/2" | 6082T6 |
| Aluminium Tube | 8 3/16" OD X 0.65" | GCQ |
| Aluminium Tube | 210MM OD X 15MM | 6082T6 |
| Aluminium Tube | 8 1/2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 8 1/2" OD X 3/4" | 6082T6 |
| Aluminium Tube | 8 1/2" OD X 1" | 6082T6 |
| Aluminium Tube | 220MM OD X 40MM | 6082T6 |
| Aluminium Tube | 9" OD X 1/4" | 6082T6 |
| Aluminium Tube | 9" OD X 1/2" | 6082T6 |
| Aluminium Tube | 9" OD X 3/4" | 6082T6 |
| Aluminium Tube | 9" OD X 1" | 6082T6 |
| Aluminium Tube | 9 1/2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 9 1/2" OD X 3/4" | 6082T6 |
| Aluminium Tube | 9 1/2" OD X 1" | 6082T6 |
| Aluminium Tube | 10" OD X 1/4" | 6082T6 |
| Aluminium Tube | 250MM OD X 10MM | 6082T6 |
| Aluminium Tube | 10" OD X 1/2" | 6082T6 |
| Aluminium Tube | 10" OD X 3/4" | 6082T6 |
| Aluminium Tube | 250MM OD X 20MM | 6082T6 |
| Aluminium Tube | 10" OD X 1" | 6082T6 |

| | | |
|----------------|-------------------|--------|
| Aluminium Tube | 260MM OD X 15MM | 6082T6 |
| Aluminium Tube | 10 1/2" OD X 1/2" | 6082T6 |
| Aluminium Tube | 10 1/2" OD X 3/4" | 6082T6 |
| Aluminium Tube | 10 1/2" OD X 1" | 6082T6 |
| Aluminium Tube | 11" OD X 1/4" | 6082T6 |
| Aluminium Tube | 11" OD X 1/2" | 6082T6 |
| Aluminium Tube | 11" OD X 3/4" | 6082T6 |
| Aluminium Tube | 11" OD X 1" | 6082T6 |
| Aluminium Tube | 11 1/2" OD X 1" | 6082T6 |
| Aluminium Tube | 12" OD X 1/4" | 6082T6 |
| Aluminium Tube | 12" OD X 1/2" | 6082T6 |

| Description | Size | Spec |
|----------------------|-------------|-------------|
| Aluminium Square Bar | 3/16" SQ | 6082T6 |
| Aluminium Square Bar | 1/4" SQ | 6082T6 |
| Aluminium Square Bar | 5/16" SQ | 6082T6 |
| Aluminium Square Bar | 3/8" SQ | 6082T6 |
| Aluminium Square Bar | 10MM SQ | 6082T6 |
| Aluminium Square Bar | 1/2" SQ | 6082T6 |
| Aluminium Square Bar | 12MM SQ | 6082T6 |
| Aluminium Square Bar | 15MM SQ | 6082T6 |
| Aluminium Square Bar | 5/8" SQ | 6082T6 |
| Aluminium Square Bar | 3/4" SQ | 6082T6 |
| Aluminium Square Bar | 20MM SQ | 6082T6 |
| Aluminium Square Bar | 7/8" SQ | 6082T6 |
| Aluminium Square Bar | 1" SQ | 6082T6 |
| Aluminium Square Bar | 25MM SQ | 6082T6 |
| Aluminium Square Bar | 1 1/4" SQ | 6082T6 |
| Aluminium Square Bar | 30MM SQ | 6082T6 |
| Aluminium Square Bar | 35MM SQ | 6082T6 |
| Aluminium Square Bar | 1 1/2" SQ | 6063T6 |
| Aluminium Square Bar | 1 1/2" SQ | 6082T6 |
| Aluminium Square Bar | 40MM SQ | 6082T6 |
| Aluminium Square Bar | 1 3/4" SQ | 6082T6 |
| Aluminium Square Bar | 2" SQ | 6082T6 |
| Aluminium Square Bar | 2 1/4" SQ | 6082T6 |
| Aluminium Square Bar | 60MM SQ | 6082T6 |
| Aluminium Square Bar | 2 1/2" SQ | 5251 F |
| Aluminium Square Bar | 2 1/2" SQ | 6082T6 |
| Aluminium Square Bar | 2 3/4" SQ | 2024T3 |
| Aluminium Square Bar | 2 3/4" SQ | 6082T6 |
| Aluminium Square Bar | 3" SQ | 2014AT4 |
| Aluminium Square Bar | 3" SQ | 6082T6 |
| Aluminium Square Bar | 3 1/4" SQ | 6082T6 |
| Aluminium Square Bar | 3 1/2" SQ | 6082T6 |
| Aluminium Square Bar | 100MM SQ | 6082T6 |
| Aluminium Square Bar | 4" SQ | 6082T6 |
| Aluminium Square Bar | 4 1/2" SQ | 6082T6 |
| Aluminium Square Bar | 5" SQ | 6082T6 |
| Aluminium Square Bar | 5 1/2" SQ | 6082T6 |
| Aluminium Square Bar | 6 1/2" SQ | 6082T6 |
| Aluminium Square Bar | 7" SQ | 6082T6 |
| Aluminium Square Bar | 8" SQ | 6082T6 |

| Description | Size | Spec |
|-------------------------|-------------|-------------|
| Aluminium Hexagonal Bar | 3/16" AF | 6082T6 |
| Aluminium Hexagonal Bar | 0.248" A/F | 2014AT4 |
| Aluminium Hexagonal Bar | 1/4" AF | 6082T6 |
| Aluminium Hexagonal Bar | 5/16" AF | 6005AT6 |
| Aluminium Hexagonal Bar | 0.375" AF | 6063T6 |
| Aluminium Hexagonal Bar | 3/8" AF | 6082T6 |
| Aluminium Hexagonal Bar | 10MM AF | 6082T6 |
| Aluminium Hexagonal Bar | 1/2" AF | 6262T9 |
| Aluminium Hexagonal Bar | 1/2" AF | 6082T6 |
| Aluminium Hexagonal Bar | 9/16" AF | 6082T6 |
| Aluminium Hexagonal Bar | 5/8" AF | 2011T3 |
| Aluminium Hexagonal Bar | 5/8" AF | 6082T6 |
| Aluminium Hexagonal Bar | 0.71" AF | 6082T6 |
| Aluminium Hexagonal Bar | 3/4" AF | 6082T6 |
| Aluminium Hexagonal Bar | 0.82" AF | 6082T6 |
| Aluminium Hexagonal Bar | 7/8" A/F | 2011T3 |
| Aluminium Hexagonal Bar | 7/8" AF | 6082T6 |
| Aluminium Hexagonal Bar | 0.92" A/F | 2014AT4 |
| Aluminium Hexagonal Bar | 0.92" AF | 2011T3 |
| Aluminium Hexagonal Bar | 0.92" AF | 6082T6 |
| Aluminium Hexagonal Bar | 15/16" A/F | 6061T6 |
| Aluminium Hexagonal Bar | 1" AF | 6082T6 |
| Aluminium Hexagonal Bar | 1.1" AF | 6082T6 |
| Aluminium Hexagonal Bar | 1 1/8" AF | 6082T6 |
| Aluminium Hexagonal Bar | 1 5/16" A/F | 2014AT4 |
| Aluminium Hexagonal Bar | 1.2" AF | 6082T6 |
| Aluminium Hexagonal Bar | 1 1/4" AF | 6082T6 |
| Aluminium Hexagonal Bar | 1.3" AF | 6082T6 |
| Aluminium Hexagonal Bar | 1 3/8" AF | 6082T6 |
| Aluminium Hexagonal Bar | 1 7/16" A/F | 2014AT4 |
| Aluminium Hexagonal Bar | 1.48" A/F | 2014AT4 |
| Aluminium Hexagonal Bar | 1.48" AF | 6082T6 |
| Aluminium Hexagonal Bar | 1 9/16" A/F | 2014AT4 |
| Aluminium Hexagonal Bar | 2" A/F | 2014AT4 |
| Aluminium Hexagonal Bar | 2.05" AF | 6082T6 |
| Aluminium Hexagonal Bar | 70MM AF | 6082T6 |

| Description | Size | Spec |
|--------------------|--------------|-------------|
| Aluminium Flat Bar | 1/4" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 3/8" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 3/8" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 10MM X 6MM | 6082T6 |
| Aluminium Flat Bar | 1/2" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 1/2" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 1/2" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 1/2" X 5/16" | 6082T6 |
| Aluminium Flat Bar | 1/2" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 1/2" X 1/16" | 6063T6 |
| Aluminium Flat Bar | 5/8" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 5/8" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 5/8" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 5/8" X 5/16" | 6082T6 |
| Aluminium Flat Bar | 5/8" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 5/8" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 18MM X 6MM | 6063T6 |
| Aluminium Flat Bar | 3/4" X 1/16" | 6063T6 |
| Aluminium Flat Bar | 3/4" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 20MM X 3MM | 6082T6 |
| Aluminium Flat Bar | 20MM X 4MM | 6082T6 |
| Aluminium Flat Bar | 3/4" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 20MM X 5MM | 6082T6 |
| Aluminium Flat Bar | 3/4" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 20MM X 6MM | 6082T6 |
| Aluminium Flat Bar | 3/4" X 5/16" | 6082T6 |
| Aluminium Flat Bar | 20MM X 8MM | 6082T6 |
| Aluminium Flat Bar | 3/4" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 20MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 3/4" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 20MM X 12MM | 6082T6 |
| Aluminium Flat Bar | 20MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 3/4" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 7/8" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 7/8" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 7/8" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 7/8" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 7/8" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 1" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 1" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 25MM X 5MM | 6082T6 |
| Aluminium Flat Bar | 1" X 1/4" | 2014AT4 |
| Aluminium Flat Bar | 1" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 25MM X 6MM | 6082T6 |
| Aluminium Flat Bar | 1" X 5/16" | 6082T6 |
| Aluminium Flat Bar | 25MM X 8MM | 6082T6 |
| Aluminium Flat Bar | 1" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 25MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 1" X 1/2" | 6061T6 |
| Aluminium Flat Bar | 1" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 25MM X 12MM | 6082T6 |
| Aluminium Flat Bar | 25MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 1" X 5/8" | 6082T6 |

| | | |
|--------------------|-----------------|----------|
| Aluminium Flat Bar | 1" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 25MM X 20MM | 6082T6 |
| Aluminium Flat Bar | 1 1/4" X 1/8" | 6063T6 |
| Aluminium Flat Bar | 1 1/4" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 30MM X 3MM | 6082T6 |
| Aluminium Flat Bar | 1 1/4" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 30MM X 5MM | 6082T6 |
| Aluminium Flat Bar | 30MM X 6MM | 5083 |
| Aluminium Flat Bar | 1 1/4" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 30MM X 6MM | 6082T6 |
| Aluminium Flat Bar | 1 1/4" X 5/16" | 6082T6 |
| Aluminium Flat Bar | 30MM X 8MM | 6082T6 |
| Aluminium Flat Bar | 30MM X 10MM | 5083 F |
| Aluminium Flat Bar | 1 1/4" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 30MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 1 1/4" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 30MM X 12MM | 6082T6 |
| Aluminium Flat Bar | 30MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 1 1/4" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 1 1/4" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 30MM X 20MM | 6082T6 |
| Aluminium Flat Bar | 1 1/4" X 1" | 6082T6 |
| Aluminium Flat Bar | 30MM X 25MM | 6082T6 |
| Aluminium Flat Bar | 1 3/8" X 1/4" | 6082T651 |
| Aluminium Flat Bar | 1 3/8" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 1 3/8" X 1 1/4" | 6063T6 |
| Aluminium Flat Bar | 1 1/2" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 40MM X 3MM | 6082T6 |
| Aluminium Flat Bar | 40MM X 4MM | 6082T6 |
| Aluminium Flat Bar | 1 1/2" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 40MM X 5MM | 6082T6 |
| Aluminium Flat Bar | 1 1/2" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 40MM X 6MM | 6082T6 |
| Aluminium Flat Bar | 1 1/2" X 5/16" | 6082T6 |
| Aluminium Flat Bar | 40MM X 8MM | 6082T6 |
| Aluminium Flat Bar | 1 1/2" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 40MM X 10MM | 6101A |
| Aluminium Flat Bar | 40MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 1 1/2" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 40MM X 12MM | 6082T6 |
| Aluminium Flat Bar | 40MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 1 1/2" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 1 1/2" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 40MM X 22MM | 6082T6 |
| Aluminium Flat Bar | 1 5/8" X 1" | 2014AT6 |
| Aluminium Flat Bar | 1 1/2" X 1" | 6082T6 |
| Aluminium Flat Bar | 40MM X 25MM | 6082T6 |
| Aluminium Flat Bar | 1 1/2" X 1 1/4" | 6082T6 |
| Aluminium Flat Bar | 40MM X 30MM | 6082T6 |
| Aluminium Flat Bar | 1 3/4" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 1 3/4" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 1 3/4" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 1 3/4" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 1 3/4" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 1 3/4" X 5/8" | 6082T6 |

| | | |
|--------------------|-----------------|---------|
| Aluminium Flat Bar | 1 3/4" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 1 3/4" X 1" | 6082T6 |
| Aluminium Flat Bar | 1 3/4" X 1 1/4" | 6082T6 |
| Aluminium Flat Bar | 1.3/4" X 1.1/2" | 6082T6 |
| Aluminium Flat Bar | 45MM X 40MM | 6082T6 |
| Aluminium Flat Bar | 2" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 2" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 50MM X 5MM | 6082T6 |
| Aluminium Flat Bar | 2" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 50MM X 6MM | 6082T6 |
| Aluminium Flat Bar | 2" X 5/16" | 6082T6 |
| Aluminium Flat Bar | 50MM X 8MM | 6082T6 |
| Aluminium Flat Bar | 2" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 50MM X 10MM | 5083 F |
| Aluminium Flat Bar | 50MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 2" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 50MM X 12MM | 6082T6 |
| Aluminium Flat Bar | 50MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 2" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 2" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 50MM X 20MM | 6082T6 |
| Aluminium Flat Bar | 2" X 1" | 6082T6 |
| Aluminium Flat Bar | 50MM X 25MM | 6082T6 |
| Aluminium Flat Bar | 2" X 1 1/4" | 6082T6 |
| Aluminium Flat Bar | 50MM X 30MM | 6082T6 |
| Aluminium Flat Bar | 2" X 1 1/2" | 6082T6 |
| Aluminium Flat Bar | 50MM X 40MM | 6082T6 |
| Aluminium Flat Bar | 2" X 1 3/4" | 6082T6 |
| Aluminium Flat Bar | 2 1/8" X 1" | 6082T6 |
| Aluminium Flat Bar | 2 1/4" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 2 1/4" X 3/8" | 2014AT6 |
| Aluminium Flat Bar | 2 1/4" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 60MM X 5MM | 6082T6 |
| Aluminium Flat Bar | 60MM X 6MM | 6082T6 |
| Aluminium Flat Bar | 60MM X 8MM | 6082T6 |
| Aluminium Flat Bar | 60MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 60MM X 12MM | 6082T6 |
| Aluminium Flat Bar | 60MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 60MM X 20MM | 6082T6 |
| Aluminium Flat Bar | 60MM X 25MM | 6082T6 |
| Aluminium Flat Bar | 60MM X 30MM | 6082T6 |
| Aluminium Flat Bar | 60MM X 40MM | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 5/16" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 3/8" | 2014T6 |
| Aluminium Flat Bar | 2 1/2" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 1" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 1 1/4" | 2014AT6 |
| Aluminium Flat Bar | 2 1/2" X 1 1/4" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 1 1/2" | 6082T6 |

| | | |
|--------------------|-----------------|---------|
| Aluminium Flat Bar | 2 1/2" X 1 3/4" | 6082T6 |
| Aluminium Flat Bar | 2 1/2" X 2" | 2014AT6 |
| Aluminium Flat Bar | 2 1/2" X 2" | 6082T6 |
| Aluminium Flat Bar | 2 3/4" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 70MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 70MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 70MM X 20MM | 6082T6 |
| Aluminium Flat Bar | 70MM X 25MM | 6082T6 |
| Aluminium Flat Bar | 70MM X 30MM | 6082T6 |
| Aluminium Flat Bar | 2 7/8" X 1" | GCQ |
| Aluminium Flat Bar | 3" X 1/8" | 2014AT6 |
| Aluminium Flat Bar | 3" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 3" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 3" X 1/4" | 2014AT6 |
| Aluminium Flat Bar | 3" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 3" X 5/16" | 6082T6 |
| Aluminium Flat Bar | 3" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 3" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 3" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 3" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 3" X 1" | 6082T6 |
| Aluminium Flat Bar | 3" X 1 1/4" | 6082T6 |
| Aluminium Flat Bar | 3" X 1 1/2" | 6061T6 |
| Aluminium Flat Bar | 3" X 1 1/2" | 6082T6 |
| Aluminium Flat Bar | 3" X 1 3/4" | 6082T6 |
| Aluminium Flat Bar | 3" X 2" | 2014AT6 |
| Aluminium Flat Bar | 3" X 2" | 6082T6 |
| Aluminium Flat Bar | 3" X 2 1/2" | 6082T6 |
| Aluminium Flat Bar | 80MM X 6MM | 5083 F |
| Aluminium Flat Bar | 80MM X 6MM | 6082T6 |
| Aluminium Flat Bar | 80MM X 8MM | 6082T6 |
| Aluminium Flat Bar | 80MM X 10MM | 5083 |
| Aluminium Flat Bar | 80MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 80MM X 12MM | 6082T6 |
| Aluminium Flat Bar | 80MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 80MM X 20MM | 6082T6 |
| Aluminium Flat Bar | 80MM X 25MM | 6082T6 |
| Aluminium Flat Bar | 80MM X 30MM | 6082T6 |
| Aluminium Flat Bar | 80MM X 40MM | 6082T6 |
| Aluminium Flat Bar | 3 1/4" X 1 7/8" | 2014AT6 |
| Aluminium Flat Bar | 3 1/4" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 3 1/4" X 1 1/4" | 6082T6 |
| Aluminium Flat Bar | 3 1/4" X 1 3/8" | 2014AT6 |
| Aluminium Flat Bar | 3 1/4" X 1 1/2" | 6082T6 |
| Aluminium Flat Bar | 85MM X 50MM | 2014AT6 |
| Aluminium Flat Bar | 3 1/2" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 3 1/2" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 3 1/2" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 3 1/2" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 3 1/2" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 3 1/2" X 1" | 6082T6 |
| Aluminium Flat Bar | 3 1/2" X 1 1/4" | 6082T6 |
| Aluminium Flat Bar | 90MM X 35MM | 2014AT6 |
| Aluminium Flat Bar | 3 1/2" X 1 1/2" | 2014AT6 |
| Aluminium Flat Bar | 3 1/2" X 1 1/2" | 6082T6 |

| | | |
|--------------------|-----------------|-----------|
| Aluminium Flat Bar | 3 1/2" X 1 3/4" | 6082T6 |
| Aluminium Flat Bar | 3 1/2" X 2" | 6082T6 |
| Aluminium Flat Bar | 90MM X 50MM | 6082T6 |
| Aluminium Flat Bar | 3 1/2" X 2 1/2" | 6082T6 |
| Aluminium Flat Bar | 3 1/2" X 3" | 6082T6 |
| Aluminium Flat Bar | 3 3/4" X 3/4" | 2014AT6 |
| Aluminium Flat Bar | 3 3/4" X 1 1/8" | 6082T6 |
| Aluminium Flat Bar | 4" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 4" X 3/16" | 6082T6 |
| Aluminium Flat Bar | 100MM X 5MM | 6082T6 |
| Aluminium Flat Bar | 100MM X 6MM | 5083 F |
| Aluminium Flat Bar | 100MM X 6MM | 2014AT6 |
| Aluminium Flat Bar | 4" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 100MM X 6MM | 6082T6 |
| Aluminium Flat Bar | 100MM X 8MM | 6082T6 |
| Aluminium Flat Bar | 4" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 100MM X 10MM | 5083 F |
| Aluminium Flat Bar | 100MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 4" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 100MM X 12MM | 6082T6 |
| Aluminium Flat Bar | 100MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 4" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 4" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 100MM X 20MM | 6082T6 |
| Aluminium Flat Bar | 4" X 1" | 7075T6511 |
| Aluminium Flat Bar | 4" X 1" | 6082T6 |
| Aluminium Flat Bar | 100MM X 25MM | 6082T6 |
| Aluminium Flat Bar | 4" X 1 1/4" | 6082T6 |
| Aluminium Flat Bar | 100MM X 30MM | 6082T6 |
| Aluminium Flat Bar | 4" X 1 1/2" | 6082T6 |
| Aluminium Flat Bar | 4" X 1 3/4" | 7075T6 |
| Aluminium Flat Bar | 4" X 2" | 6082T6 |
| Aluminium Flat Bar | 4" X 2 1/4" | 6082T6 |
| Aluminium Flat Bar | 4" X 2 1/2" | 6082T6 |
| Aluminium Flat Bar | 4" X 3" | 6082T6 |
| Aluminium Flat Bar | 4 1/2" X 1" | 2014AT6 |
| Aluminium Flat Bar | 4 1/2" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 120MM X 5MM | 6082T6 |
| Aluminium Flat Bar | 120MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 120MM X 12MM | 6082T6 |
| Aluminium Flat Bar | 120MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 120MM X 20MM | 6082T6 |
| Aluminium Flat Bar | 120MM X 25MM | 6082T6 |
| Aluminium Flat Bar | 120MM X 30MM | 6082T6 |
| Aluminium Flat Bar | 120MM X 90MM | 6082T6 |
| Aluminium Flat Bar | 5" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 5" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 5" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 5" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 5" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 5" X 1" | 6082T6 |
| Aluminium Flat Bar | 5" X 1 1/4" | 6082T6 |
| Aluminium Flat Bar | 5" X 1 1/2" | 6082T6 |
| Aluminium Flat Bar | 5" X 2" | 6082T6 |
| Aluminium Flat Bar | 5" X 2 1/2" | 6082T6 |

| | | |
|--------------------|-----------------|---------|
| Aluminium Flat Bar | 5" X 3" | 6082T6 |
| Aluminium Flat Bar | 5" X 3 1/4" | 6082T6 |
| Aluminium Flat Bar | 5" X 4" | 6082T6 |
| Aluminium Flat Bar | 5 1/2" X 4" | 6082T6 |
| Aluminium Flat bar | 5 1/2" X 4 1/2" | 2014AT6 |
| Aluminium Flat Bar | 6" X 1/8" | 6082T6 |
| Aluminium Flat Bar | 150MM X 5MM | 6082T6 |
| Aluminium Flat Bar | 6" X 1/4" | 6082T6 |
| Aluminium Flat Bar | 150MM X 6MM | 6082T6 |
| Aluminium Flat Bar | 6" X 3/8" | 6082T6 |
| Aluminium Flat Bar | 150MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 6" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 150MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 6" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 6" X 3/4" | 6082T6 |
| Aluminium Flat Bar | 6" X 1" | 6082T6 |
| Aluminium Flat Bar | 6" X 1 1/2" | 6082T6 |
| Aluminium Flat Bar | 6" x 2" | 6082T6 |
| Aluminium Flat Bar | 6" X 2 1/2" | 6082T6 |
| Aluminium Flat Bar | 6" X 2 7/8" | GCQ |
| Aluminium Flat Bar | 6" X 3" | 6082T6 |
| Aluminium Flat Bar | 6" X 3 1/2" | 6082T6 |
| Aluminium Flat Bar | 6" X 4" | 6082T6 |
| Aluminium Flat Bar | 6" X 5" | 7075T6 |
| Aluminium Flat Bar | 6" X 5" | 6082T6 |
| Aluminium Flat Bar | 6 1/2" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 7" X 1" | 2014T6 |
| Aluminium Flat Bar | 200MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 8" X 1/2" | 6082T6 |
| Aluminium Flat Bar | 200MM X 15MM | 6082T6 |
| Aluminium Flat Bar | 8" X 5/8" | 6082T6 |
| Aluminium Flat Bar | 200MM X 20MM | 6082T6 |
| Aluminium Flat Bar | 200MM X 125MM | 2024T3 |
| Aluminium Flat Bar | 9" X 1" | GCQ |
| Aluminium Flat Bar | 230MM X 1/2" | 2014AT6 |
| Aluminium Flat Bar | 250MM X 10MM | 6082T6 |
| Aluminium Flat Bar | 10" X 47MM | 6082T6 |
| Aluminium Flat Bar | 12" X 1" | 2014T6 |
| Aluminium Flat Bar | 12" X 1 1/2" | 2014T6 |
| Aluminium Flat Bar | 305MM X 40MM | 2007 |

| Description | Size | Spec |
|--------------------------------|----------------------------|-------------|
| Aluminium Box Tube | 1/2" X 1/2" X 1MM | 6063T6 |
| Aluminium Box Tube | 1/2" X 1/2" X 16G | 6063T6 |
| Aluminium Box Tube | 3/4" X 3/4" X 1MM | 6063T6 |
| Aluminium Box Tube Rad Corners | 3/4" X 3/4" X 16G R | 6063T6 |
| Aluminium Box Tube | 3/4" X 3/4" X 16G | 6082T6 |
| Aluminium Box Tube | 3/4" X 3/4" X 10G | 6082T6 |
| Aluminium Box Tube | 1" X 1/2" X 16G | 6063T6 |
| Aluminium Box Tube Rad Corners | 1" X 1" X 16G R | 6063T6 |
| Aluminium Box Tube | 1" X 1" X 16G | 6063T6 |
| Aluminium Box Tube | 1" X 1" X 16G | 6082T6 |
| Aluminium Box Tube | 1" X 1" X 10G | 6082T6 |
| Aluminium Box Tube | 30MM X 30MM X 3MM | 6082T6 |
| Aluminium Box Tube | 1 1/4" X 1 1/4"X16G | 6063T6 |
| Aluminium Box Tube | 1 1/4" X 1 1/4"X16G | 6082T6 |
| Aluminium Box Tube | 1 1/4" X 1 1/4"X10G | 6082T6 |
| Aluminium Box Tube | 1 1/2" X 3/4" X16G | 6005AT6 |
| Aluminium Box Tube | 1 1/2" X 3/4" X10G | 6063T6 |
| Aluminium Box Tube | 1 1/2" X 1" X 16G | 6063T6 |
| Aluminium Box Tube Rad Corners | 1 1/2" X 1" X 10G 2MM RADS | 6082T6 |
| Aluminium Box Tube | 1 1/2" X 1" X 10G | 6082T6 |
| Aluminium Box Tube | 1 1/2" X 1 1/2"X16G | 6063T6 |
| Aluminium Box Tube | 1 1/2" X 1 1/2"X16G | 6082T6 |
| Aluminium Box Tube | 1 1/2" X 1 1/2"X10G | 6082T6 |
| Aluminium Box Tube | 40MM X 20MM X 2MM | 6063T6 |
| Aluminium Box Tube Rad Corners | 40MM X 30MM X 2.5MM | 6063T6 |
| Aluminium Box Tube | 40MM X 40MM X 3MM | 6082T6 |
| Aluminium Box Tube Rad corners | 40MM X 40MM X 1.5MM | 6063T6 |
| Aluminium Box Tube | 45MM X 45MM X 1.5MM | 6082T6 |
| Aluminium Box Tube | 1 3/4" X 1 3/4"X10G | 6082T6 |
| Aluminium Box Tube | 2" X 1" X 16G | 6082T6 |
| Aluminium Box Tube | 2" X 1" X 10G | 6082T6 |
| Aluminium Box Tube | 2" X 1 1/2" X 10G | 6082T6 |
| Aluminium Box Tube | 50MM X 40MM X 3MM | 6082T6 |
| Aluminium Box Tube | 2" X 2" X 16G | 6063T6 |
| Aluminium Box Tube | 2" X 2" X 16G | 6082T6 |
| Aluminium Box Tube | 2" X 2" X 10G | 6082T6 |
| Aluminium Box Tube | 2" X 2" X 3/16" | 6082T6 |
| Aluminium Box Tube | 2" X 2" X 1/4" | 6063T6 |
| Aluminium Box Tube | 2" X 2" X 1/4" | 6082T6 |
| Aluminium Box Tube | 50MM X 25MM X 3MM | 6082T6 |
| Aluminium Box Tube | 60MM X 40MM X 3MM | 6082T6 |
| Aluminium Box Tube Rad Corners | 60MM X 40MM X 2MM | 6082T6 |
| Aluminium Box Tube | 60MM X 60MM X 4MM | 6082T6 |
| Aluminium Box Tube | 2 1/2" X 1 1/2"X10G | 6082T6 |
| Aluminium Box Tube | 2 1/2" X 2 1/2"X10G | 6082T6 |
| Aluminium Box Tube | 2 1/2"X2 1/2"X3/16" | 6082T6 |
| Aluminium Box Tube | 3" X 1" X 10G | 6082T6 |
| Aluminium Box Tube | 3" X 1 1/2" X 14G | 6082T6 |
| Aluminium Box Tube | 3" X 1 1/2" X 10G | 6082T6 |
| Aluminium Box Tube | 3" X 1 3/4" X 10G | 6082T6 |
| Aluminium Box Tube | 3" X 2" X 10G | 6082T6 |
| Aluminium Box Tube | 3" X 2" X 1/4" | 6082T6 |
| Aluminium Box Tube | 3" X 3" X 10G | 6082T6 |

| | | |
|--------------------|-----------------------|---------|
| Aluminium Box Tube | 3" X 3" X 3/16" | 6082T6 |
| Aluminium Box Tube | 3" X 3" X 1/4" | 6082T6 |
| Aluminium Box Tube | 80MM X 40MM X 4MM | 6082T6 |
| Aluminium Box Tube | 80MM X 80MM X 2MM | 6063T6 |
| Aluminium Box Tube | 4" X 1" X 10G | 6082T6 |
| Aluminium Box Tube | 4" X 1 3/4" X 10G | 6082T6 |
| Aluminium Box Tube | 4" X 2" X 10G | 6082T6 |
| Aluminium Box Tube | 100MM X 50MM X 3MM | 6082T6 |
| Aluminium Box Tube | 4" X 2" X 1/4" | 6082T6 |
| Aluminium Box Tube | 4" X 3" X 10G | 6082T6 |
| Aluminium Box Tube | 4" X 3" X 1/4" | 6082T6 |
| Aluminium Box Tube | 100MM X 100MM X 2MM | 6063T6 |
| Aluminium Box Tube | 4" X 4" X 10G | 6082T6 |
| Aluminium Box Tube | 4" X 4" X 1/4" | 6082T6 |
| Aluminium Box Tube | 120MM X 60MM X 4MM | 6082T6 |
| Aluminium Box Tube | 120MM X 80MM X 6.75MM | 6082T6 |
| Aluminium Box Tube | 120MM X 120MM X 5MM | 6082T6 |
| Aluminium Box Tube | 5" X 2" X 3MM | 6082T6 |
| Aluminium Box Tube | 5" X 2" X 1/4" | 6082T6 |
| Aluminium Box Tube | 6" X 2" X 10G | 6082T6 |
| Aluminium Box Tube | 6" X 2" X 1/4" | 6082T6 |
| Aluminium Box Tube | 6" X 3" X 3/8" | 6082T6 |
| Aluminium Box Tube | 150MM X 100MM X 3MM | 6005AT6 |
| Aluminium Box Tube | 150MM X 150MM X 3MM | 6063T6 |
| Aluminium Box Tube | 6" X 3" X 3MM | 6082T6 |
| Aluminium Box Tube | 200MM X 45MM X 3MM | 6063T6 |
| Aluminium Box Tube | 200MM X 80MM X 6MM | 6082T6 |
| Aluminium Box Tube | 250MM X 50MM X 4MM | 6005AT6 |